



Assembly Instruction for 6250ML TYPE PLUS 62

ALUMINUM BOTTLES U.N. APPROVED AS SINGLE PACKAGINGS (1B1).

This bottle has been tested and approved with the following components:

Option 1 : Group II, III

- 1/ ALUMINUM BOTTLE**
- 2/ LDPE PLUG**
- 3/ PP CAP WITH ALPE/PEE LINER**

After filling, insert the sealing plug to full depth by pushing it down, screw the cap to the following recommended torque: 89 Inch per lbs.

Recommended Torque Wrench. Item # TORQ009
Custom chuck. Item # ADAPT62

Option 2 : Group II, III

- 1/ ALUMINUM BOTTLE**
- 2/ PP CAP WITH PTFE (Teflon) LINER**

After filling, screw the cap to the following recommended torque: 89 Inch per lbs.

Recommended Torque Wrench. Item # TORQ009
Custom chuck. Item # ADAPT62



Option 3 : Group II, III

- 1/ ALUMINUM BOTTLE**
- 2/ PP CAP WITH ALPE/PEE LINER**

After filling, screw the cap to the following recommended torque: 89 Inch per lbs.

Recommended Torque Wrench. Item # TORQ009
Custom chuck. Item # ADAPT62

Labeling and marking are the shipper responsibility.
Elemental Container assumes no responsibility for the package integrity or compliance to the U.N. hazardous goods regulations unless all package components are assembled per the above instructions and supplied by Elemental Container.

Product compatibility with the aluminum is the customer responsibility and must be in accordance with the Packaging instructions of the 49CFR. Container compliance is predicated on a product maximum density of 1.2 (H₂O = 1.0).

UN certificates are available upon request.



Elemental Container Inc . 860 Springfield Road South . Union, New Jersey 07083 . USA
Telephone 908.687.7720 . 800. 577.7624 . Fax 908.687.5157 . www.aluminumbottles.com
Last update 05/10/19